


**DogBone Wet Inlay**  
**EPC Class 1 Gen 2, ISO 18 000-6C**  
**Impinj M730**  
**Sales code 3007995**

### Mechanical dimensions

A1 x A2	Antenna size	94 x 24 mm	± 0,5 mm	3.701 x 0.945 in
B1 x B2	Die-cut size	97 x 27 mm	± 0,2 mm	3.819 x 1.063 in
C	Web width	100 mm	± 0,5 mm	3.937 in
D	Pitch, length per piece MD	30 mm	± 1,5 mm	1.181 in
E	Die-cut to web edge	1.5 mm	± 1,5 mm	0.059 in
F	Die-cut to register mark	0 mm	± 1,0 mm	0.000 in
I	Minimum size of register mark (width x length)	5 x 3 mm		0.197 x 0.118 in
U	Corner radius	3 mm		0,118 in



### Electrical characteristics

Integrated Circuit (IC)	Impinj M730
Air interface protocol	EPC Class 1 Gen 2, ISO 18000-6C
Operation frequency	860 - 960 MHz

Memory	128 bit EPC
--------	-------------


### General characteristics of transponder

Operating temperature (electronics parts)	-40 °C / +85 °C	-40 °F / 185 °F
ESD voltage immunity	± 2 kV peak HBM	
Shelf life: From the date of manufacture 2 years in	+20 °C, 50 % RH	68 °F, 50 % RH
Bending diameter (D)	> 50 mm, tension less than 10 N	

### Delivery form

Transponder format	Die-cut	
Transponder face material	Clear PET 12	
Transponder antenna material	Aluminum	
Transponder adhesive	RA-2	
- labelling temperature	min. +5 °C	min. 41 °F
- usage temperature	-40°C - 150 °C	-40 °F - 302 °F
- peel	min. 15 N / 25 mm (FTM 1)	
Final inspection	100 %, known faulty ones marked	
Minimum delivery yield	97 %	
Reel Label	Reel number, Material number, Material description, Yield, Qty of functional inlays, Qty of non-functional inlays, Date	

### Structure



### Delivery details

Appearance	Single row reel form
Reel core	Paper core inner diameter 76 mm (3 in)
Winding of the reel	Face out
Reel size	5000 pcs/reel

**Disclaimer:**

SMARTRAC reserves the right to change its products and services at any time without notice. Our recommendations are based on our best knowledge and experience. As the products are used outside our control we cannot take responsibility for any damage that may be caused when using the product. Use extra care in handling the product.

This technical specification replaces all earlier ones.

Version 1  
Update date 26 March 2021  
Author SMARTRAC /  
Approved SMARTRAC / 3/29/2021 Kelvin Low/Smartrac

